



YAZ486TC12

by Burndy
Catalog ID: YAZ486TC12

Copper Tubing Terminal; 1 Hole W/insp Window; 2500 kcmil; 1/2 IN Stud;
7.34 IN L; 3.46 IN W; Wire Strip Length: 4-3/4 IN

Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810241080
UPC 12 Digit	7818102410800

Dimensions

Dimension - B Length fraction	4-11/16 in
Dimension - B Length inch	4.69 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.52 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	186 mm
Dimension - Length Overall inch	7.34 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Pad Width inch	3.46 in
Dimension - Strip Length inch	4-3/4
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	2500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)