

YAZ8C2TC10E2FX

by Burndy
Catalog ID: YAZ8C2TC10E2FX

Copper compression terminal, #10 stud, 2 hole, long barrel, #8 Flex



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	194
Type	Long Barrel, Tin Plated
UPC	781810324226
UPC 12 Digit	7818103242266

Dimensions

Dimension - B Length inch	0.75 in
Dimension - Length Side B inch	2.33 in
Dimension - Pad Width inch	0.41 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	8 (37/#24) DLO
Conductor - Copper DLO Size Range	8 (37/#24) DLO
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex G Size Range	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex H Size Range	8 AWG
Conductor - Copper Str Size	8 AWG

Conductor - Copper Str Size Range	8 AWG
Conductor - CopperWeld C Solid Size	8 AWG
Conductor - CopperWeld Solid Size Range	8 AWG
Conductor - Material	Copper

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)