



YAZ8C2TC10SL

by Burndy
Catalog ID: YAZ8C2TC10SL

Prop 65 Notice

HYLUG SLOTTED,COPPER COMPRESSION TERMINAL,2 hole, DieIndex 49

Product Details

General

| | |
|--------------------------------------|--------------------------------|
| Color Code | Red |
| Connector Type | Terminal |
| Die Index | 49 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Type | Long Barrel, Skive, Tin Plated |
| UPC | 781810289976 |
| UPC 12 Digit | 7818102899766 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 3/4 in |
| Dimension - B Length inch | 0.75 in |
| Dimension - Hole Size fraction | 1/5 |
| Dimension - Hole Size inch | 0.21 in |
| Dimension - Hole Size mm | 5 mm |
| Dimension - L Length Overall mm | 56 mm |
| Dimension - Length Overall inch | 2.21 in |
| Dimension - N inch | 0.25 in |
| Dimension - Outside Diameter inch | 0.27 in |
| Dimension - Pad Width inch | 0.44 in |
| Dimension - Strip Length inch | 13/16 |
| Dimension - Stud Size inch | #10 |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

Conductor Related

| | |
|---|-------------------------|
| Conductor - Copper DLO Size | 8 (37/#24) DLO |
| Conductor - Copper DLO Size Range | 8 (37/#24) DLO |
| Conductor - Copper Flex G Size | 8 AWG |
| Conductor - Copper Flex G Size Range | 8 AWG |
| Conductor - Copper Flex H Size | 8 AWG |
| Conductor - Copper Flex H Size Range | 8 AWG |
| Conductor - Copper Flex I Size | 8 AWG |
| Conductor - Copper Flex I Size Range | 8 AWG |
| Conductor - Copper Flex K Size | 8 AWG |
| Conductor - Copper Flex K Size Range | 8 AWG |
| Conductor - Copper Flex M Size | 8 AWG |
| Conductor - Copper Flex M Size Range | 8 AWG |
| Conductor - Copper Solid Size | 8 AWG |
| Conductor - Copper Solid Size Range | 8 AWG |
| Conductor - Copper Str Navy Size | 23 (7) Navy |
| Conductor - Copper Str Size | 8 AWG |
| Conductor - CopperWeld C Solid Size | 8 AWG |
| Conductor - CopperWeld Solid Size Range | 8 AWG |
| Conductor - CopperWeld Str Size | 8 A AWG;8 C AWG;8 D AWG |
| Conductor - CopperWeld Str Size Range | 8 A AWG-8 D AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)