

YAZ8C2TC14E2FX

by Burndy
Catalog ID: YAZ8C2TC14E2FX

Prop 65 Notice

Cu compression long barrel flex conductor, 2 holes/W/ insp window, #8 weld(37/24), #3 AWG,1/4" stud, Red, 49 index



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	49
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Yes
Plating Type	Tin-Electro plated
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810324332
UPC 12 Digit	7818103243322

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.810 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size inch	0.437 in
Dimension - Hole Size mm	7 mm
Dimension - Inside Diameter inch	0.18 in
Dimension - L Length Overall mm	62 mm
Dimension - Length Overall inch	2.450 in
Dimension - Length Side B inch	2.45 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.27 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	1 in
Dimension - Z inch	0.34 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	8 (37/#24) DLO
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex K Size	8 AWG
Conductor - Copper Flex M Size	8 AWG
Conductor - Copper Str Size	8 AWG
Conductor - CopperWeld Str Size	8 A AWG;8 C AWG;8 D AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)