

YAZV102TC1445

by Burndy
Catalog ID: YAZV102TC1445

Cu Tubing Hylug (2 Hole Code); 2 Holes with Inspection Window; #14-
#10 AWG Code; 600V-35kV; 1/4" stud; Long; Compression; 0.27 in BCD



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810196885
UPC 12 Digit	7818101968855

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Height inch	0.77 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.03 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	3/4
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)