

YAZV102TC14E1

by Burndy
Catalog ID: YAZV102TC14E1

Cu Compression Terminal, 2 Holes, W/Insp Window, #14 - #10 AWG (Code), 1/4 IN Bolt Size, 3/4 IN Wire Strip Length



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810545201
UPC 12 Digit	7818105452011

Dimensions

Dimension - B Length inch	0.69 in
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.53 in
Dimension - Length Side B inch	2.53 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	3/4
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG
Conductor - Material	Copper
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)