

YAZV1C2TC14E2FX

by Burndy
Catalog ID: YAZV1C2TC14E2FX

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window,
1(225/#24) DLO, #1 AWG, 1/4" stud, .75" spacing, Green, 11 or 375 Index



Product Details

General

Color Code	Green
Connector Type	Terminal
Die Index	11;375
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228357
UPC 12 Digit	7818102283577

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	80 mm
Dimension - Length Overall inch	3.16 in
Dimension - Length Side B inch	3.16 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.75 in
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1 (225/#24) DLO
Conductor - Copper Flex G Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor - Copper Str Size	1 AWG
Conductor - CopperWeld Str Size	1 F AWG;1 G AWG;1 J AWG;1 K AWG;1 N AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)