

# YAZV1C2TC516FX

by Burndy  
Catalog ID: YAZV1C2TC516FX

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window,  
1(225/#24) DLO, #1 AWG, 5/16" stud, 1" spacing, Green, 11 or 375 Index



## Product Details

### General

|                                      |                    |
|--------------------------------------|--------------------|
| Color Code                           | Green              |
| Connector Type                       | Terminal           |
| Die Index                            | 11;375             |
| Feature - Barrel Style               | Skived             |
| Feature - Barrel Type                | Long               |
| Material                             | Copper             |
| Physical Attribute - Number of Holes | 2                  |
| Plated                               | Y                  |
| Plating Type                         | Tin                |
| Trade Name                           | HYLUG™             |
| Type                                 | Long Barrel, Skive |
| UPC                                  | 781810228364       |
| UPC 12 Digit                         | 7818102283644      |

### Dimensions

|                                   |          |
|-----------------------------------|----------|
| Dimension - B Length fraction     | 1-3/8 in |
| Dimension - B Length inch         | 1.38 in  |
| Dimension - Bolt Hole Size inch   | 0.33 in  |
| Dimension - Bolt Size fraction    | 5/16     |
| Dimension - Hole Size inch        | 0.33 in  |
| Dimension - Hole Size mm          | 8 mm     |
| Dimension - L Length Overall mm   | 88 mm    |
| Dimension - Length Overall inch   | 3.47 in  |
| Dimension - Length Side B inch    | 3.47 in  |
| Dimension - N inch                | 0.34 in  |
| Dimension - Outside Diameter inch | 0.51 in  |
| Dimension - Pad Width inch        | 0.75 in  |
| Dimension - Strip Length inch     | 1-7/16   |
| Dimension - Z inch                | 0.37 in  |
| Physical Attribute - Tongue Angle | Straight |

## Electrical Ratings

|                          |       |
|--------------------------|-------|
| Rating - KVA             | 35 kV |
| Rating - Minimum Voltage | 600   |
| Voltage - Maximum        | 35000 |

## Conductor Related

|                                 |                                         |
|---------------------------------|-----------------------------------------|
| Conductor - Copper DLO Size     | 1 (225/#24) DLO                         |
| Conductor - Copper Flex G Size  | 1 AWG                                   |
| Conductor - Copper Flex H Size  | 1 AWG                                   |
| Conductor - Copper Flex I Size  | 1 AWG                                   |
| Conductor - Copper Flex K Size  | 1 AWG                                   |
| Conductor - Copper Flex M Size  | 1 AWG                                   |
| Conductor - Copper Str Size     | 1 AWG                                   |
| Conductor - CopperWeld Str Size | 1 F AWG;1 G AWG;1 J AWG;1 K AWG;1 N AWG |
| Conductor - Material            | Copper                                  |

## Certifications and Compliance

|                                    |     |
|------------------------------------|-----|
| Certification - CSA Approved       | Yes |
| Certification - ETL                | No  |
| Certification - UL Recognized      | No  |
| Certification - cULus              | No  |
| Standards - RoHS Compliance Status | CM  |
| UL Listed                          | Yes |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)