



YAZV282TC38FXSL

by Burndy
Catalog ID: YAZV282TC38FXSL

CULUG-4/0FX-LG-W/PORT-SL

Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810532522
UPC 12 Digit	7818105325222

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.64 in
Dimension - Pad Width inch	1.14 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	3/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Conductor - Material	Copper
----------------------	--------

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)