



YAZV28NT38FX

by Burndy
Catalog ID: YAZV28NT38FX

Prop 65 Notice

Cu compression long barrel-Flex conductor, Single hole W/ insp window, 550/24.4/0 weld.4/0AWG, 600 V-35 kV, 3/8" stud, Purple, 15 index

Product Details

General

Color Code	Purple
Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810241646

Dimensions

Dimension - B Length fraction	1-5/8 in
Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.01 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	0.94 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	4/0 (550/#24)
Conductor - Copper Flex G Size	4/0
Conductor - Copper Flex H Size	4/0
Conductor - Copper Flex I Size	4/0
Conductor - Copper Flex K Size	4/0
Conductor - Copper Flex M Size	4/0
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size Range	4/0
Conductor - CopperWeld Str Size	4/0 E;4/0 EK;4/0 F;4/0 G;4/0 V

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)