

YAZV292NT516FX

by Burndy
Catalog ID: YAZV292NT516FX

2 Hole HYLUG Cu Compression Terminal, Narrow Tongue, 4/0 Flex, 5/16" stud, Yellow, 16 Index, Wire Strip Length 2-1/16" L



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810324493

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Diameter Min Size inch	1.71 in
Dimension - Hole Size inch	0.33 in
Dimension - Inside Diameter inch	0.64 in
Dimension - L Length Overall mm	109 mm
Dimension - Length Overall inch	4.28 in
Dimension - Length Side B inch	4.62 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.80 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	2-1/16
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.37 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)