

YAZV4C2NT10FX

by Burndy
Catalog ID: YAZV4C2NT10FX

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 5(91/#24)
- 4(105/#24) DLO, #4 AWG Weld, #4 AWG Code, #10 stud, .62" spacing,
Gray, 8 or 346 Index



Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	8;346
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228173
UPC 12 Digit	7818102281733

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	69 mm
Dimension - Length Overall inch	2.70 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.41 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	5 (91/#24) DLO;4 (105/#24) DLO
Conductor - Copper DLO Size Range	5 (91/#24) DLO-4 (105/#24) DLO
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - CopperWeld Str Size	4 A AWG;4 D AWG;4 N AWG;4 P AWG
Conductor - CopperWeld Str Size Range	4 A AWG-4 P AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)