

YAZV4C2TC14FX90

by Burndy
Catalog ID: YAZV4C2TC14FX90

Prop 65 Notice

Cu Comp Terminal Flex Cond(W/Port), 2 Hole/W/InspWindow, #4 Weld, 5(91/#24)-4(105/#24)DLO Flex, #4 AWG Code, 600 V-35 kV, 1/4" Stud, 90 Deg Bent, Lng bbl.

Two hole, Copper compression terminal flex conductor, long barrel



Product Details

General

| | |
|--------------------------------------|---------------------|
| Application | For Flex Conductors |
| Color Code | Gray |
| Connector Type | Terminal |
| Die Index | 8;346 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 2 |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | TERMINALS, HYLUG |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive |
| UPC | 781810230541 |
| UPC 12 Digit | 7818102305411 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-1/4 in |
| Dimension - B Length inch | 1.25 in |
| Dimension - Bolt Hole Size inch | 0.27 in |
| Dimension - Height inch | 1.69 in |
| Dimension - Hole Size inch | 0.27 in |
| Dimension - Hole Size mm | 7 mm |
| Dimension - L Length Overall mm | 39 mm |
| Dimension - Length Overall inch | 1.55 in |
| Dimension - N inch | 0.31 in |
| Dimension - Outside Diameter inch | 0.38 in |
| Dimension - Pad Width inch | 0.55 in |
| Dimension - Strip Length inch | 1-5/16 |
| Dimension - Z inch | 0.33 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|---------------------------------------|---------------------------------|
| Conductor - Copper DLO Size | 5 (91/#24) DLO;4 (105/#24) DLO |
| Conductor - Copper DLO Size Range | 5 (91/#24) DLO-4 (105/#24) DLO |
| Conductor - Copper Flex G Size | 4 AWG |
| Conductor - Copper Flex G Size Range | 4 AWG |
| Conductor - Copper Flex H Size | 4 AWG |
| Conductor - Copper Flex H Size Range | 4 AWG |
| Conductor - Copper Flex I Size | 4 AWG |
| Conductor - Copper Flex I Size Range | 4 AWG |
| Conductor - Copper Flex K Size | 4 AWG |
| Conductor - Copper Flex K Size Range | 4 AWG |
| Conductor - Copper Flex M Size | 4 AWG |
| Conductor - Copper Flex M Size Range | 4 AWG |
| Conductor - Copper Str Size | 4 AWG |
| Conductor - CopperWeld Str Size | 4 A AWG;4 D AWG;4 N AWG;4 P AWG |
| Conductor - CopperWeld Str Size Range | 4 A AWG-4 P AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)