

# YAZV6C2TC10FX90SL

by Burndy  
Catalog ID: YAZV6C2TC10FX90SL

Prop 65 Notice

Copper Tubing Terminal, 6 (61/#24) DLO, #6 Code, 30 Navy, #10 Bolt, 7 or 374 Index



## Product Details

### General

Color Code	Blue
Connector Type	Terminal
Die Index	7;374
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810217412
UPC 12 Digit	7818102174122

### Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Height inch	0.97 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	#10
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	6 (61/#24) DLO
Conductor - Copper DLO Size Range	6 (61/#24) DLO
Conductor - Copper Flex G Size	6 AWG
Conductor - Copper Flex G Size Range	6 AWG
Conductor - Copper Flex H Size	6 AWG
Conductor - Copper Flex H Size Range	6 AWG
Conductor - Copper Flex I Size	6 AWG
Conductor - Copper Flex I Size Range	6 AWG
Conductor - Copper Flex K Size	6 AWG
Conductor - Copper Flex K Size Range	6 AWG
Conductor - Copper Flex M Size	6 AWG
Conductor - Copper Flex M Size Range	6 AWG
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size Range	6 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor - Copper Str Size	6 AWG
Conductor - CopperWeld C Solid Size	6 AWG
Conductor - CopperWeld Solid Size Range	6 AWG
Conductor - CopperWeld Str Size	6 A AWG;6 C AWG;6 D AWG
Conductor - CopperWeld Str Size Range	6 A AWG-6 D AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)