

YBA36FX

by Burndy
Catalog ID: YBA36FX

Cu Break-Away HYLUG Compression Terminals, NEMA std, 450 kcmil, 1/2" stud, 6.59" L, Brown, 20 Index



Product Details

General

Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin Plated
Trade Name	HYLUG™
UPC	781810485286

Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.69 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.59 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.47 in
Dimension - Strip Length inch	2-3/4 in
Dimension - Stud Size inch	1/2 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.64 in
Length	6.59 in
Outside Diameter	1.19 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 kcmil (1100/24)
Conductor - Copper Flex G Size	450 kcmil Flex
Conductor - Copper Flex H Size	450 kcmil Flex
Conductor - Copper Flex I Size	444.4 kcmil
Conductor - Copper Flex K Size	444.4 kcmil
Conductor - Copper Flex M Size	444.4 kcmil
Conductor - Copper Str Size	450 kcmil
Conductor - Nominal Diameter	0.876, 0.878, 0.894, 0.933, 0.940, 1.240
Conductor Size	444.4 kcmil (1100/24), 450 kcmil Flex
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • CU C DLO-Size • CU C Flex I-Size • CU C Flex K-Size • CU C Flex M-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)