



YBM261/4LD

by Burndy
Catalog ID: YBM261/4LD

Prop 65 Notice

Lead Plated Flag Type, Ring Tongue Electrolytic Cu Terminal

Product Details

General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Lead
Trade Name	HYLUG™
UPC	781810044919
UPC 12 Digit	7818100449199

Dimensions

Dimension - B Length fraction	15/16 in
Dimension - B Length inch	0.95 in
Dimension - D inch	1.17 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.93 in
Dimension - N inch	0.45 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.95 in
Dimension - Z inch	0.72 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)