



YBM26L14MMBR

by Burndy
Catalog ID: YBM26L14MMBR

Prop 65 Notice

Cu Flag Terminal, 2/0 Class I, Wire Strip Length- 7/8 " L

Product Details

General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	N
Plating Type	Unplated
UPC	781810460818
UPC 12 Digit	7818104608188

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - D inch	0.94 in
Dimension - Hole Size inch	0.61 in
Dimension - Length Overall inch	1.72 in
Dimension - N inch	0.42 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.81 in
Dimension - Strip Length inch	7/8
Dimension - Z inch	0.52 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24)
Conductor - Copper DLO Size Range	2/0 (375/#24)
Conductor - Copper Flex I Size	2/0
Conductor - Copper Flex I Size Range	2/0
Conductor - Copper Str Aircraft Size	AN 00
Conductor - Copper Str Aircraft Size Range	AN 00

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)