



## YBM26L2

by Burndy  
Catalog ID: YBM26L2

Prop 65 Notice

Flag Type, Ring Tongue Electrolytic Cu Terminal, 2/0 AWG, 1/4" stud, 598 Index

## Product Details

### General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810455586

### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.66 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.84 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.45 in
Physical Attribute - Tongue Angle	90 Degree

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)