



YBM26L3BR

by Burndy
Catalog ID: YBM26L3BR

Prop 65 Notice

Extruded Cu, Flag type Terminal, Ring-Tongue, 2/0 AWG FLEX, 1/2" stud, 1.96" L, Unplated

Product Details

General

Connector Type	Terminal - Ring
Die Index	598
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810460825

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.84 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Length Overall inch	1.96 in
Dimension - N inch	0.48 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.91 in
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.61 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Standards - RoHS Compliance Status

CM

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)