



## YBM26L

by Burndy  
Catalog ID: YBM26L

Prop 65 Notice

Extruded Copper Flag Terminal, 2/8 IN Stud, 598 Index

## Product Details

### General

Connector Type	Terminal - Ring
Die Index	598
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810026328

### Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.71 in
Dimension - N inch	0.36 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.84 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.49 in
Physical Attribute - Tongue Angle	90 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24)
Conductor - Copper Flex I Size	2/0
Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## For further technical assistance, please contact us

### BURNDY Headquarters

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)