



YBM4CL4

by Burndy
Catalog ID: YBM4CL4

Prop 65 Notice

One Piece Extruded Hylugs Copper Terminal, Ring Tongue, #4 AWG Flex Class I, 4(105/#24) DLO, #4 AWG Code, #8 - #10 stud, 56 Index

Product Details

General

Connector Type	Terminal - Ring
Die Index	56
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026267

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Length Overall inch	1.18 in
Dimension - N inch	0.27 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	4 (105/#24)
Conductor - Copper Flex I Size	4
Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Size	4
Conductor - Copper Str Size Range	4

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	800 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)