



YBM6CL9

by Burndy
Catalog ID: YBM6CL9

Prop 65 Notice

One Piece Extruded Hylugs Copper Terminal, Ring Tongue, #6 AWG Flex Class I, #6 AWG Code, #8 - #10 stud, 55 Index

Product Details

General

Connector Type	Terminal - Ring
Die Index	55
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026298

Dimensions

Dimension - B Length fraction	9/16 in
Dimension - B Length inch	0.47 in
Dimension - Bolt Hole Size inch	0.2 in
Dimension - Length Overall inch	1.09 in
Dimension - N inch	0.27 in
Dimension - Outside Diameter inch	0.37 in
Dimension - Pad Width inch	0.53 in
Dimension - Strip Length inch	1/2
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.36 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	6 (61/#24)
Conductor - Copper Flex I Size	6
Conductor - Copper Str Aircraft Size	AN 6
Conductor - Copper Str Size	6
Conductor - Copper Str Size Range	6

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)