



YBM8CT4

by Burndy
Catalog ID: YBM8CT4

Prop 65 Notice

Flag Type, Ring Tongue Electrolytic Cu Terminal, #8 AWG, 3/8" stud, 54 Index

Product Details

General

Connector Type	Terminal - Ring
Die Index	54
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810039854

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.59 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Length Overall inch	1.19 in
Dimension - N inch	0.36 in
Dimension - Outside Diameter inch	0.32 in
Dimension - Pad Width inch	0.66 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	8 (37/#24)
Conductor - Copper Flex I Size	8
Conductor - Copper Flex K Size	8
Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8

Conductor - Copper Str Size Range	8
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)