


# YC1U1

by Burndy  
Catalog ID: YC1U1

Prop 65 Notice

Figure 6- shaped, wide range-taking aluminum compression tap connector Run: Al & Cu: 2 - 1 Kcmil, ACSR: 2, Tap: 6 - 1 AWG, ACSR: 6 -2



## Product Details

### General

Die Index	D
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810121252
UPC 12 Digit	7818101212522

### Dimensions

Dimension - Height inch	1.62 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

### Conductor Related

Conductor - ACSR Str Run	2 Str
Conductor - ACSR Str Tap Range	6 AWG - 2 AWG
Conductor - AL Str Run Range	2 AWG - 1 AWG
Conductor - AL Str Tap Range	6 AWG-2 AWG
Conductor - Copper Solid Tap Range	6 AWG
Conductor - Copper Str Run Range	2 AWG-1 AWG
Conductor - Copper Str Tap Range	6 AWG-2 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)