

YC25A4

by Burndy
Catalog ID: YC25A4

Prop 65 Notice

Al Compression Tap(C-Shaped),1/0 Str. Al/ACSR(Run), #6 - #4 Str.
Al/ACSR(Tap), 1.50" L



Product Details

General

Die Index	C
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810123607
UPC 12 Digit	7818101236077

Dimensions

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

Conductor Related

Conductor - ACSR Str Run	1/0 Str
Conductor - ACSR Str Tap Range	6 AWG - 4 AWG
Conductor - AL Str Run	1/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG
Conductor - AL Str Tap Range	6 AWG - 4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)