



YC25L12TN

by Burndy
Catalog ID: YC25L12TN

Prop 65 Notice

Cu Thin Wall C-Tap, Compression, 1/0 - #2 AWG(Main), #2 - #12 AWG(Tap), 600 V, Tin Plated

Product Details

General

Accessory Type	6" FRPT Kit
Application	6" Fire-Rated Poke-Through Series
Application - For Use On	Concrete
Color Code	Orange
Die Index	14
Finish Type	Brushed Brass Plated Cover
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Copper Assorted Materials
Material - Mounting Hardware	Mounting Hardware Included
Number Of Outlets	(2) 50% Left Side Sub Plates- (3) Extron® AAP Opening, (5) Extron® MAAP Opening, 50% Left Side, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Left Side Sub Plate- (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings
Plated	Y
Plating Type	Tin - Electro Plated
Style	FRPT - Complete Kits
Temperature Rating	194
UPC	783585443393
UPC 12 Digit	7818100402499

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - Strip Length inch	1-13/16

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Cable Entry	Through Cover
Conductor - Copper Solid Run	2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Run Range	2 AWG-1/0 AWG

Conductor - Copper Solid Tap	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	12 AWG-2 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0
Conductor - Copper Str Run Range	2 AWG-1/0
Conductor - Copper Str Tap	12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	12 AWG-2 AWG

Certifications and Compliance

Certification - ETL	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • cULus Listed • Meets ADA Standards • UL 514A Listed
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	150
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)