

YC26A26

by Burndy
Catalog ID: YC26A26

Prop 65 Notice

Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, Prefilled with Penetrox.

Features: Range-Taking, C-Shaped Aluminum Compression Tap, Or Dead-Ending Connector Designed To Eliminate Effects Of Cold Flow, Can Be Gripped In Tool And Slipped Over Line For Easy Crimping, Pre-Filled With PENETROX Joint Compound And Stripsealed, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U-D Die, (3), Y45 Tool, U-D Die With PT-6515 Adapter, (3), Y46 Tool, U-D Die With PUADP-1 Adapter, (3), Die Index: D Element A, Compressed / Compact: No, Conductor Size (run - Range): 1/0 - 2/0 AWG, Conductor Type: Run: Aluminum, Tap: Aluminum, Shape: C, Conductor Size (tap Range): 2/0 AWG



Product Details

General

Application	For Combinations Of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors
Die Index	D
Material	Aluminum
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810124826
UPC 12 Digit	7818101248266

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in

Conductor Related

Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap	2/0 Str
Conductor - AL Str Run	1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	2/0 Str
Conductor - AL Str Tap Range	2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)