



## YC26A2

by Burndy  
Catalog ID: YC26A2

Prop 65 Notice

Al Compression Tap(C-Shaped),1/0 - 2/0 Str.Al/ACSR(Run), #2  
Str.Al/ACSR(Tap), 2.56" L

## Product Details

### General

|              |                   |
|--------------|-------------------|
| Material     | Aluminum          |
| Plated       | N                 |
| Plating Type | Unplated          |
| Trade Name   | CRIMPIT™          |
| Type         | YC-A, YC-U Series |
| UPC          | 781810105054      |
| UPC 12 Digit | 7818101050544     |

### Dimensions

|                                 |         |
|---------------------------------|---------|
| Dimension - Height inch         | 1.38 in |
| Dimension - L Length Overall mm | 65 mm   |
| Dimension - Length Overall inch | 2.56 in |

### Conductor Related

|                              |                   |
|------------------------------|-------------------|
| Conductor - ACSR Str Run     | 2 AWG             |
| Conductor - ACSR Str Tap     | 2 Str             |
| Conductor - AL Str Run Range | 1/0 AWG - 2/0 AWG |
| Conductor - AL Str Tap       | 2 Str             |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)