

YC26C2

by Burndy
Catalog ID: YC26C2

Prop 65 Notice

CU Compression C Shape Compression Connector, 600 Volts to 35 Kv, Run: 1/0 Str. - 2/0 Str., Tap: 8 Sol. - 2 Str.

Features: Range-Taking Connector: Lowers Inventory Requirements, Compact Size: Easy To Tape And Insulate Connection, Manufactured From High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Economical: Provides Low Installed Cost, 8A - Use CRIMPITS Accommodating 6 Stranded Copper, 6A - Use CRIMPITS Accommodating 4 Stranded Copper, 4A - Use CRIMPITS Accommodating 2 Stranded Copper, 2A - Use CRIMPITS Accommodating 1/0 And 2/0 Copper, Use PUADP-1 Adapter When Using U Dies In The Y46 HYPRESS, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750, Y45 Tool, U-O Die, (1), U-E Die, (3), Y46 Tool, U-O Die With PUADP-1 Adapter, (1), U-E Die With PUADP-1 Adapter, (3), Crimpit For 1 Stranded Copper (run): 1 AWG Stranded, Die Index: O Element A, Crimpit For 1 Stranded Copper (tap): 1 Or 2 AWG Stranded, Conductor Size (run - Range): 1/0 - 2/0 AWG, Conductor Type: Run: Commercial Stranded Copper, Tap: Commercial Stranded Copper, Shape: C, Conductor Size (tap Range): 8 - 2 AWG



Product Details

General

Application	For Making Tap Or Parallel Copper Connections
Die Index	E or O
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Trade Name	CRIMPIT™
Type	YC-C Series
UPC	781810114803
UPC 12 Digit	7818101148033

Dimensions

Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.92 in

Conductor Related

Conductor - Copper Str Run Range	1/0 -2/0 AWG
Conductor - Copper Str Tap Range	8 Sol. - 2 Str

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)