

YC28A25

by Burndy
Catalog ID: YC28A25

Prop 65 Notice

Range-taking, C-shaped AL compression tap, Run: Aluminum: 3/0- 4/0, ACSR: 3/0-4/0, Tap: Aluminum: 1/0- 1/0, ACSR: 1/0- 1/0



Product Details

General

Die Index	H
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810125427
UPC 12 Digit	7818101254277

Dimensions

Dimension - Height inch	1.61 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in

Conductor Related

Conductor - AAAC 5005 Run	195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 5005 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 5005 Tap	123.3 (7) kcmil
Conductor - AAAC 5005 Tap Range	123.3 (7) kcmil
Conductor - AAAC 6201 Run	195.7 (7) kcmil;246.9 (7) kcmil
Conductor - AAAC 6201 Run Range	195.7 (7) kcmil-246.9 (7) kcmil
Conductor - AAAC 6201 Tap	123.3 (7) kcmil
Conductor - AAAC 6201 Tap Range	123.3 (7) kcmil
Conductor - ACSR Cmpt Run	3/0 AWG;4/0 AWG
Conductor - ACSR Cmpt Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Cmpt Tap	1/0 AWG
Conductor - ACSR Cmpt Tap Range	1/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG

Conductor - AL Str Tap	1/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)