

# YC28A2

by Burndy  
Catalog ID: YC28A2

Prop 65 Notice

Range-taking, C-shaped AL compression tap, Run: Aluminum: 3/0- 4/0, ACSR: 3/0-4/0, Tap: Aluminum: 6- 2, ACSR: 6-2



## Product Details

### General

Die Index	H
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810125120
UPC 12 Digit	7818101251200

### Dimensions

Dimension - Height inch	1.61 in
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in

### Conductor Related

Conductor - ACSR Cmpt Run	3/0 AWG;4/0 AWG
Conductor - ACSR Cmpt Run Range	3/0 AWG-4/0 AWG
Conductor - ACSR Str Run Range	3/0 AWG - 4/0 AWG
Conductor - ACSR Str Tap Range	6 AWG - 2 AWG
Conductor - AL Str Run	3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	3/0 AWG - 4/0 AWG
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	6 AWG - 2 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)