

YC2A4

by Burndy
Catalog ID: YC2A4

Prop 65 Notice

Range-taking, C-shaped AL compression tap, or dead-ending connector designed to eliminate the effects of cold flow, "C" Die index



Product Details

General

Die Index	C
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810122105
UPC 12 Digit	7818101221055

Dimensions

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

Conductor Related

Conductor - AAAC 5005 Run	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil
Conductor - AAAC 6201 Run	48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil
Conductor - ACSR Cmpt Run	4 AWG;3 AWG;2 AWG
Conductor - ACSR Cmpt Run Range	4 AWG-2 AWG
Conductor - ACSR Cmpt Tap	6 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG
Conductor - ACSR Str Run Range	4 AWG - 2 AWG
Conductor - ACSR Str Tap	6 Str
Conductor - AL Str Run	2 AWG
Conductor - AL Str Run Range	2 Sol. - 2 Str

Conductor - AL Str Tap	4 AWG
Conductor - AL Str Tap Range	4 Sol. - 4 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)