


YC4U1

by Burndy
Catalog ID: YC4U1

Prop 65 Notice

Figure 6- shaped, wide range-taking aluminum compression tap connector for smaller primary service taps and secondary service drops
Pre-filled with PENETROX,Run(Al & Cu): 4 Sol. -4Str.



Product Details

General

Die Index	D
Plated	N
Plating Type	Unplated
Type	YC-A, YC-U Series
UPC	781810123102
UPC 12 Digit	7818101231022

Conductor Related

Conductor - AAAC 5005 Run	48.69 (7) kcmil
Conductor - AAAC 5005 Run Range	48.69 (7) kcmil
Conductor - AAAC 5005 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 5005 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - AAAC 6201 Run	48.69 (7) kcmil
Conductor - AAAC 6201 Run Range	48.69 (7) kcmil
Conductor - AAAC 6201 Tap	30.58 (7) kcmil;48.69 (7) kcmil;77.47 (7) kcmil
Conductor - AAAC 6201 Tap Range	30.58 (7) kcmil-77.47 (7) kcmil
Conductor - ACSR Cmpt Run	4 AWG
Conductor - ACSR Cmpt Run Range	4 AWG
Conductor - ACSR Cmpt Tap	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG
Conductor - ACSR Cmpt Tap Range	6 AWG-1 AWG
Conductor - AL Str Run Range	4 Sol. - 4 Str.
Conductor - AL Str Tap	6 AWG;4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	6 Sol. - 1 Str.
Conductor - Copper Solid Run Range	4 Sol. - 4 Str.
Conductor - Copper Solid Tap Range	6 Sol. - 1 Str.
Conductor - Copper Str Run Range	4 Sol. - 4 Str.
Conductor - Copper Str Tap Range	6 Sol. - 1 Str.

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)