



## YC6L12TN

by Burndy  
Catalog ID: YC6L12TN

Prop 65 Notice

Cu Thin Wall C-Tap, Compression, #6 - #8 AWG(Main), #8 - #12 AWG(Tap), 600 V, Tin Plated

## Product Details

### General

Color Code	Gray
Connector Type	C-Tap
Die Index	8
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	YC-L Series
UPC	781810243350
UPC 12 Digit	7818102433500

### Dimensions

Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.33 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.25 in
Dimension - Strip Length inch	5/8

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Run Range	8 AWG-6 AWG
Conductor - Copper Str Tap	12 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Str Tap Range	12 AWG-8 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)