

# YCA322N

by Burndy  
Catalog ID: YCA322N

Copper compression lug designed for terminating copper conductors to switch pads and other substation switch yard apparatus, 6.72 IN L



## Product Details

### General

Connector Type	Terminal
Die Index	209
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810014738

### Dimensions

Dimension - B Length inch	2.78 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.72 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.67 in
Dimension - Strip Length inch	2 5/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)