

## YCAB314N

by Burndy  
Catalog ID: YCAB314N

Prop 65 Notice

Cast Cu Alloy Tongue Terminal With Cu Sleeve, 4 NEMA Holes, 350 Kcmil  
Cu(12, 19, 37 Str), 1/2" Stud, 1.75" Spacing, 267 Index



## Product Details

### General

Connector Type	Terminal
Die Index	267
Material	Copper Alloy
Physical Attribute - Number of Holes	4
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810035382

### Dimensions

Dimension - B Length fraction	2-33/50 in
Dimension - B Length inch	2.66 in
Dimension - D inch	2.00 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	178 mm
Dimension - Length Overall inch	7.00 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.17 in
Dimension - Pad Width inch	3.00 in
Dimension - Strip Length inch	1 3/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.63 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)