



# YCAK28A2G1

by Burndy  
Catalog ID: YCAK28A2G1

Prop 65 Notice

Aluminum Terminal, 4/0 Str. Cu,Al Conc.& Compact, 317 or 705 Index

## Product Details

### General

Die Index	317;705
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810248
UPC 12 Digit	7818108102488

### Dimensions

Dimension - B Length fraction	5-5/8 in
Dimension - B Length inch	1.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - D inch	3 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.63 in
Dimension - Pad Width inch	1.25 in

### Conductor Related

Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG
Conductor - Copper Str Size Range	4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)