



YCAK29A2G1

by Burndy
Catalog ID: YCAK29A2G1

Prop 65 Notice

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 5.63 IN L

Product Details

General

Die Index	317;705
Material	Aluminum Alloy, Cast
Physical Attribute - Pad Configuration	2 Hole NEMA
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810262
UPC 12 Digit	7818108102622

Dimensions

Dimension - B Length fraction	5-5/8 in
Dimension - B Length inch	1.56 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - D inch	3 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.63 in
Dimension - Pad Width inch	1.25 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSR Str Size	4/0 AWG - 250 kcmil
Conductor - ACSR Str Size Range	4/0 AWG - 250 kcmil
Conductor - AL Str Size	250 kcmil
Conductor - AL Str Size Range	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Copper Str Size Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)