

YCAK33R4N

by Burndy
Catalog ID: YCAK33R4N

Prop 65 Notice

Al Compression terminal, 336.4 Kcmil ACSR(26-7, 30-7) str 397.5 Kcmil Al(19)Str, .56"stud, 7.34"L, , 316 index.

Features: Compression Terminal, Conductor Type: ACSR/6201/5005 (Compressed/Compact), Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U316 Die, (4), Y45 Tool, U316 Die With PT-6515 Adapter, (4), Y46 Tool, U316 Die With PUADP-1 Adapter, (4), Y48B Tool, C316 Die, (2), Y60BHU Tool, L316 Die, (2), Die Index: 316



Product Details

General

Application	For ACSR/6201/5005 (Compressed/Compact), Aluminum
Die Index	316
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Trade Name	HYLUG™
Type	YCAK-R-N, Terminal
UPC	781810810231
UPC 12 Digit	7818108102311

Dimensions

Dimension - B Length inch	3.05 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.34 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	336.4 (26-7) kcmil;336.4 (30-7) kcmil
Conductor - ACSR Str Size Range	336.4 (26-7) kcmil;336.4 (30-7) kcmil
Conductor - AL Str Size	397.5 kcmil
Conductor - AL Str Size Range	397.5 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)