



YCAK361R2G2

by Burndy
Catalog ID: YCAK361R2G2

Cast Aluminum Alloy Terminal, 2 Pad Holes, 477 kcmil (19,37) Al , 397.5 kcmil (26-7) ACSR

Product Details

General

| | |
|---------------------------|---------------|
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| UPC | 781810016800 |
| UPC 12 Digit | 7818100168000 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Length Overall inch | 7.25 in |
| Dimension - Pad Width inch | 1.25 in |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 4 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)