

YCAK45R4N

by Burndy
Catalog ID: YCAK45R4N

Prop 65 Notice

Aluminum Compression Terminal, 795 (26-7, 54-7) ACSR 900(61, 91),954(37, 61),1000(61) Al, 1/2" Stud.

Features:Aluminum Compression Terminals



Product Details

General

Application	For AAC(STR,Compressed,compact), ACSR AND AAAC
Die Index	352
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Type	YCAK-R-N
UPC	781810016794
UPC 12 Digit	7818100167944

Dimensions

Dimension - B Length inch	5.25 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	9.64 in
Dimension - Pad Width inch	4.00 in

Conductor Related

Conductor - ACSR Str Size	795 kcmil (54-7 STR)
Conductor - AL Str Size Range	900 kcmil (61,91 STR), 954 kcmil (37,61 STR),1000 kcmil (61 STR)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)