



YCB1U1

by Burndy
Catalog ID: YCB1U1

Prop 65 Notice

Aluminum CRIMPIT™ Hot Tap, ACSR: 2 (6-1) AWG-2 (7-1) AWG, AL or CU:
2 AWG-1 AWG

Product Details

General

Die Index	D
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810151471
UPC 12 Digit	7818101514711

Dimensions

Dimension - Bail Size	2
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.625 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in

Conductor Related

Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG;1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)