

# YCB25R

by Burndy  
Catalog ID: YCB25R

Prop 65 Notice

Permanent compression hot-line clamp adapter with aluminum run and copper bail. Permits hot-line tapping without arcing or chafing damage to aluminum conductor, Aluminum:1/0 (7, 19).

Features: Permanent Compression Hot-Line Clamp Adapter With Aluminum Run And Copper Bail, Accommodates Any Standard Copper Hotline Clamp On Bail Elements, Permits Hot-Line Tapping Without Arcing Or Chafing Damage To Aluminum Conductor, Installed With Standard Tools And Dies, With Splice, Bail Size: 2 AWG Solid, Conductor Size (run - Range): 4/0 AWG - 80 KCMIL, Conductor Type: ACSR, Aluminum, 6201, 5005, Die Index: C Element A, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-C Die, (4), Y35, Y750 Tool, U-C Die, (2), Y45 Tool, U-C Die With PT-6515 Adapter, (2), Y46 Tool, U-C Die With PUADP-1 Adapter, (2)



## Product Details

### General

Application	For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Die Index	C
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	CRIMPIT
Type	Stirrups
UPC	781810151716
UPC 12 Digit	7818101517166

### Dimensions

Dimension - Bail Size	2
Dimension - D inch	2.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	4.91 in
Dimension - L Length Overall mm	246 mm
Dimension - Length Overall inch	9.69 in

### Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG;80 (8/1) Grouse kcmil
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-80 (8/1) Grouse kcmil
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)