

YCB26AU2G1

by Burndy
Catalog ID: YCB26AU2G1

Prop 65 Notice

Aluminum Cable CRIMPIT™, ACSR: 3 (6-1) AWG-1/0 (6-1) AWG, AL or CU:
2 AWG-2/0 AWG



Product Details

General

Die Index	O
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014059
UPC 12 Digit	7818100140599

Dimensions

Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.50 in

Conductor Related

Conductor - ACSR Str Size Range	3 (6-1) AWG-1/0 (6-1) AWG
Conductor - AL Str Size Range	2 AWG-2/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)