

YCB27R

by Burndy
Catalog ID: YCB27R

Prop 65 Notice

Stirrup Connector, Aluminum: 3/0 AWG, ACSR: 3/0 AWG



Product Details

General

Die Index	L
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810152256
UPC 12 Digit	7818101522566

Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5 in
Dimension - L Length Overall mm	283 mm
Dimension - Length Overall inch	11.14 in
Dimension - Width inch	1.12 in
Dimension - Width mm	28.5 mm

Conductor Related

Conductor - ACSR Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)