

YCB28U26

by Burndy
Catalog ID: YCB28U26

Prop 65 Notice

Cable CRIMPIT™, 1/0(6-1) AWG-4/0(6-1) AWG, ACSR: 1/0 AWG-4/0 AWG
Cu or Al



Product Details

General

Die Index	H
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810152584
UPC 12 Digit	7818101525844

Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height fraction	2
Dimension - Height inch	2.06 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.125 in

Conductor Related

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Size Range	1/0 AWG-4/0 AWG
Conductor - Copper Str Size	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Str Size Range	1/0 AWG-4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR Str-Size • AL Str-Size • CU Str-Size

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)