

YCB28U2G1

by Burndy
Catalog ID: YCB28U2G1

Prop 65 Notice

Combines figure 6-shaped aluminum CRIMPIT tap connector with tin-plated copper bail. Can be gripped in tool and slid over line for easy installation.

Features: Combines Figure 6 -Shaped Aluminum CRIMPIT Tap Connector With Tin-Plated Copper Bail, Can Be Gripped In Tool And Slipped Over Line For Easy Installation, Five Sizes Take Range From 4 AWG To 600 MCM, Prefilled With PENETROX Joint Compound And Stripsealed



Product Details

General

Application	For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Die Index	D3
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	COMPRESSION TAP CONNECTOR, CABELOK CRIMPIT
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014073
UPC 12 Digit	7818100140733

Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.70 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.69 in
Dimension - Width inch	0.97 in
Dimension - Width mm	25 mm

Conductor Related

Conductor - ACSR Str Size	3/0 (6-1) AWG; 4/0 (6-1) AWG
Conductor - ACSR Str Size Range	3/0 (6-1) AWG-4/0 (6-1) AWG
Conductor - AL Str Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Conductor Type	<ul style="list-style-type: none">• ACSR Str-Size• AL Str-Size• CU Str-Size
----------------	-------------------------------------------------------------------------------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)