

YCB2R

by Burndy
Catalog ID: YCB2R

Prop 65 Notice

Permanent compression hot-line clamp adapter with aluminum run and copper bail. Permits hot-line tapping without arcing or chafing damage to aluminum conductor, Aluminum: 2 Str. - 6 Sol.

Features: Permanent Compression Hot-Line Clamp Adapter With Aluminum Run And Copper Bail, Accommodates Any Standard Copper Hotline Clamp On Bail Elements, Permits Hot-Line Tapping Without Arcing Or Chafing Damage To Aluminum Conductor, Installed With Standard Tools And Dies, With Splice, Bail Size: 2 AWG Solid, Conductor Size (run - Range): 6 - 2 AWG, Conductor Type: ACSR, Aluminum, 6201, 5014, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W-BG Die, (2), BG Die, (6), Y35, Y750 Tool, U-BG Die, (2), Y45 Tool, U-BG Die With PT-6515 Adapter, (2), Y46 Tool, U-BG Die With PUADP-1 Adapter, (2), Die Index: BG Element A



Product Details

General

Application	For Aluminum, ACSR, 6201, 5005, Compressed And Compact Conductors
Die Index	BG
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	CRIMPIT
Type	Stirrups
UPC	781810151501
UPC 12 Digit	7818101515011

Dimensions

Dimension - Bail Size	0.25 in
Dimension - D inch	2.50 in
Dimension - F Width Center to Center inch	2.50 in
Dimension - Height inch	3.75 in
Dimension - L Length Overall mm	227 mm
Dimension - Length Overall inch	8.95 in
Dimension - Width inch	0.72 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Str Size	4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	4 AWG;2 AWG

Conductor - AL Str Size Range	4 AWG-2 AWG
-------------------------------	-------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)