

YCB2U3G1

by Burndy
Catalog ID: YCB2U3G1

Prop 65 Notice

Cable CRIMPIT™, 6(6-1) AWG,-2(7-1) AWG ACSR, 6(7) AWG-3(7) AWG Cu or Al



Product Details

General

Die Index	O
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Trade Name	CRIMPIT™
Type	Stirrups
UPC	781810014042
UPC 12 Digit	7818100140422

Dimensions

Dimension - Bail Size	0.258 in
Dimension - D inch	4.25 in
Dimension - F Width Center to Center inch	4.00 in
Dimension - Height inch	1.30 in
Dimension - L Length Overall mm	63.5 mm
Dimension - Length Overall inch	2.50 in
Dimension - Width inch	0.72 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - ACSR Str Size	6 (6-1) AWG;2 (7-1) AWG
Conductor - ACSR Str Size Range	6 (6-1) AWG-2 (7-1) AWG
Conductor - AL Str Size	6 AWG;3 AWG
Conductor - AL Str Size Range	6 AWG-3 AWG
Conductor - Copper Str Size	6 AWG;3 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR Str-Size • AL Str-Size • CU Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)