

YCB321R

by Burndy
Catalog ID: YCB321R

Prop 65 Notice

Stirrup Connector, Aluminum: 336.4 kcmil-350 kcmil, ACSR: 300(26/7) kcmil, 336.4(18/1) kcmil



Product Details

General

Die Index	M
Material	Aluminum
Material - Bail	Copper
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Type	Stirrups
UPC	781810153017
UPC 12 Digit	7818101530177

Dimensions

Dimension - Bail Size	0.324 in
Dimension - D inch	3.50 in
Dimension - F Width Center to Center inch	3.50 in
Dimension - Height inch	5.39 in
Dimension - L Length Overall mm	324 mm
Dimension - Length Overall inch	12.75 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

Conductor Related

Conductor - ACSR Str Size	300.0 (26/7) Ostrich kcmil; 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	336.4 kcmil; 350 kcmil
Conductor - AL Str Size Range	336.4 kcmil-350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)